

3 ft SuperSpeed USB 3.0 to eSATA Cable Adapter

StarTech ID: *USB3S2ESATA*



The USB3S2ESATA USB 3.0 to eSATA Adapter Cable lets you connect an external SATA (eSATA) device or enclosure to a host computer through USB 3.0, in a single convenient package. The adapter cable combines USB 3.0 and eSATA cables into an integrated cable, with no external power source or driver installation required, for simple and hassle-free installation - No assembly or searching for the right cable required.

With support for SuperSpeed USB 3.0 connectivity at transfer rates up to 5 Gbps (10 times faster than USB 2.0), and backward compatibility with USB 2.0, the USB 3.0 to eSATA adapter cable provides a fast and easy-to-use Plug-and-Play experience for home, office or laptop users alike.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Laptop users who do not want to bother with having to assemble or carry multiple cables
- Home or office users who would not need to move the eSATA enclosure frequently (fixed distance/location)
- Connect an eSATA enclosure via the more commonly available USB interface

Features

- SuperSpeed USB 3.0 compliant host interface, with supported data transfer rates of up to 5 Gbps
- eSATA interface compliant with SATA revision 2 and other SATA revisions, with supported data transfer rates up to 3 Gbps
- Integrated 1m (3.3ft) USB 3.0 cable and 30cm (1ft) eSATA cable
- No driver or software installation required
- Backward compatible with USB 2.0 systems, with support for USB 2.0 transfer rates of up to 480 Mbps
- Built-in Link/Activity LED indicator
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

Warranty	2 Years
Chipset ID	LucidPort - USB300
Drive Connectors	1 - eSATA (7 pin; Data) Plug
Host Connectors	1 - USB 3.0 A (9 pin; SuperSpeed) Male
Type and Rate	USB 3.0 - 5 Gbit/s
Type and Rate	SATA II (3 Gbps)
Port Multiplier	No
Max Drive Capacity	Tested up to 2.0 TB
OS Compatibility	Windows XP (32/64-bit)/ Server 2003 (32/64-bit)/ Server 2008 R2/ Vista (32/64-bit)/ 7 (32/64-bit)/ 8 (32/64-bit) Mac OS 10.4/ 10.5/ 10.6/ 10.7/ 10.8
Color	Black
Enclosure Type	Plastic
Product Length	1.4 m [4.5 ft]
Product Weight	81 g [2.9 oz]
LED Indicators	1 - Link/Activity
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Humidity	5% ~ 85% RH
System and Cable Requirements	Available USB port
Note	If used with the Apple Mac OS operating system, this device will function in USB 2.0 mode only. eSATA port does not support Port Multiplier.
Shipping (Package) Weight	131 g [4.6 oz]
Included in Package	1 - USB 3.0 to eSATA cable
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

