



Meaco 40L High Performance Dehumidifier

- ✓ 40 litre capacity
- ✓ Available with electronic or manual controls
- ✓ Built in pump – no tank
- ✓ Available in various colours
- ✓ Proven design
- ✓ 2 speed fan
- ✓ 1 – 24 hour timer
- ✓ Suitable for flood drying and general dehumidification in areas up to 400 cubic metres



Model	Meaco 40L dehumidifier
Power consumption	550 watts
Power supply	220-240V / 50Hz
Dehumidifying capacity	40 litres / day @ 30°C and 80%rh
Capacity water container	n/a, pump only. 1.8m height gain
Air flow	180m ³ /h
Operating range	5 – 35°C
Dimensions (w x d x h)	410 x 250 x 710mm
Net weight	21Kgs
Gross weight	24Kgs