

## NETWORK 2700 SERVICE SET

The set with all essential tools for the assembly and maintenance of networks



### 2700 **BERNSTEIN** NETWORK with tool set

2701 Case with zip fastener, without tools

#### Description:

In an elegant black nylon case with zip fastener and velvet grey lining 23 special tools are clearly arranged in pockets.

**Outside dimensions: 320 x 250 x 100 mm (when closed)**

**Weight with tools: 2.750 kg**

#### Tool set:

No.	Description of individual tools	No.	Description of individual tools
2-601	<b>IC-tweezers, nickel-plated</b> , 125 mm, for gripping, inserting and removing IC's	4-775	<b>Plastic sprung handle for socket wrenches</b>
3-125-1	<b>Micro side cutters</b> , 110 mm, for soft wire up to 0.8 mm and hard wire up to 0.3 mm, chrome-plated, with BERNSTEIN-INSULATION	5-161	<b>Clamping scissors</b> , 130 mm, stainless, with serrated gripping jaws
3-235-1	<b>Telephon pliers</b> , 160 mm, chrome-plated, with BERNSTEIN-INSULATION	5-0601	<b>Rotary coaxial cable stripper</b> for cable types RG 58, RG 59 and RG 62
3-815-1	<b>Wire strippers</b> , 155 mm, with adjusting screw for all wire thicknesses, chrome-plated, with BERNSTEIN-INSULATION	6-203	<b>Socket wrench</b> , 6.0 mm, chrome vanadium, nickel plated, without handle
3-0605	<b>Combination-crimping pliers</b> for connector types, 6P/6C, 6P/4C, 6P/2C, 8P/8C	6-205	<b>Socket wrench</b> , 8.0 mm, chrome vanadium, nickel plated, without handle
3-0611	<b>Crimping pliers</b> for BNC- and TNC-coaxial connectors	6-207	<b>Socket wrench</b> , 10.0 mm, chrome vanadium, nickel plated, without handle
4-141	<b>Screwdriver</b> with special square BERNSTEIN handle, blade made from chrome vanadium, 75 x 3.5 mm, chrome-plated, with black tip	6-772	<b>Adjustable wrench</b> , chrome vanadium, 150 mm, jaw opening 0 - 18 mm
4-143	<b>Screwdriver</b> as above, 125 x 5.5 mm, chrome-plated, with black tip	6-965 L	<b>TORX-Screwdriver</b> , size T 10, with bore-hole in the tip, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, black tip
4-255	<b>Cross-recess screwdriver</b> size 0, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip, blade length 60 mm	6-966 L	<b>TORX-Screwdriver</b> , size T 15, as above, with bore-hole in the tip
4-256	<b>Cross-recess screwdriver</b> size 1, as above, blade length 80 mm	6-967 L	<b>TORX-Screwdriver</b> , size T 20, as above, with bore-hole in the tip
4-257	<b>Cross-recess screwdriver</b> size 2, as above, blade length 100 mm	8-390	<b>Desoldering pump</b> , 195 mm long, 20 mm Ø
		8-396	<b>Gas-soldering-iron Portasol</b> , 10 - 60 W, maximum temperature up to 450° C