

INOX HIGH-GRADE STEEL PLIERS

For **use in cleanrooms** (autoclavable)
antiseptic or in ESD protected areas.

Stainless steel, Swaged, Box joint construction 

With screwed stainless double leaf spring

Extremely fine polished, abrasionproof, easy to clean

On request with inserted carbide cutting edges

On request with ESD hand guard

The perfect pliers for works in following industries:

Aerospace - chemical - electronic -

Medical and dental technique - food production -

Shipbuilding - oil and gas production



33-115



33-215



33-135



33-235



33-255



33-275

No.	Length		Finish	cutting capacity mm Ø			Weight g
	mm	inches		Soft wire	Medium hard	Hard wire	

Side cutters

with very slim rounded head
for finest operations

33-115	110	4 3/8	without side face	1.1	0.4	-	36
--------	-----	-------	-------------------	-----	-----	---	----

Side cutters

with very slim rounded head

33-215	115	4 1/2	with side face	1.1	0.6	0.2	53
--------	-----	-------	----------------	-----	-----	-----	----

Oblique top cutters

straight head, flush cutting

33-135	110	4 3/8	without side face	0.8	0.6	0.2	40
--------	-----	-------	-------------------	-----	-----	-----	----

Top end cutters

bent, extremely slim, flush cutting

33-235	120	4 3/4	without side face	0.4	0.2	-	43
--------	-----	-------	-------------------	-----	-----	---	----

Snipe nose pliers

extremely slim, straight, short jaws

33-255	120	4 3/4	with plain jaws				43
--------	-----	-------	-----------------	--	--	--	----

Flat nose pliers

extremely slim, straight, short jaws

33-275	120	4 3/4	with plain jaws				44
--------	-----	-------	-----------------	--	--	--	----

SET OF ELECTRONICS PLIERS

33-100 **BERNSTEIN** Set of INOX steel pliers

3-piece set INOX high grade steel pliers in a wallet of nylon

No.	Description of individual tools	Weight: 220 g
33-215	Side cutters , 115 mm, with side face, for soft wire up to 1.1 mm, for medium hard wire up to 0.6 mm Ø, for hard wire up to 0,2 mm Ø	
33-255	Snipe nose pliers , 120 mm, plain jaws	
33-275	Flat nose pliers , 120 mm, plain jaws	

