

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com

Item # 531-SWHOX, Hercules Heavy duty Foot Switch - OX Shield



Hercules Heavy duty Foot Switch - OX Shield

- Rugged cast metal enclosure has sufficient weight to keep the switch from sliding when being operating
- All models have a neoprene cover gasket plus O-rings on the activating shaft and a separate ground screw
- In all maintained contact models the release is accomplished by simply pressing the latch with a light forward movement of the toe. The release is placed under the full shield so falling objects cannot easily release it
- Oversize "O" and "OX" shield models accept oversized safety shoes and metatarsal foot guards. The "OX" shield has an additional 3/4inch (19.1 mm) opening height as compared to the "O" shield
- Painted alert orange
- single 3/4" -14 NPT threaded conduit entry is standard
- 3 holes provided for rigid mounting to the floor or equipment

SPECIFICATIONS

Features	<ul style="list-style-type: none"> • Driptight • Dusttight • Watertight • Oiltight
Stages	Single
Circuit	SPDT
Form	C
Electrical Rating	1 H.P. 125-250 VAC Heavy pilot duty 250 Vac max. 20A 125-250 VAC
Construction/Standards	NEMA Type 2, 4 & 13 UL Enclosure 2, 4 & 13 CSA Enclosure 2, 4 & 13 EN 60529 Degree of Protection IP56
Size	9 x 5 3/4 x 4 3/4 Inch
Weight Approx.	8 lbs
Note	S-Denotes Momentary Contact-Press to start - release to stop, D-Denotes Maintained Contact-Press to start - Release Latch to stop, OX-Denotes extra oversize shield models.