

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com

Item # 971-SY, Aquiline Foot Switch



Aquiline Foot Switch

- Maximum versatility, total performance
- SPDT, DPDT, or two-stage Operation.
- Rustproof and corrosionproof reinforced polymeric material for rugged duty.
- Two stage model has cast zinc cover and formed steel base
- Non-skid base pad.
- Raised ribs on treadle for positive traction during operation.
- Attractive non-glare finish. Custom colors, and color matching available with quantity orders.
- Integrated adjustable strain relief clamp accommodates cord sizes from .250 Dia. to .400 Dia.

SPECIFICATIONS

Description	Momentary
Color	Yellow
Circuit	SPDT
Form	C
Electrical Rating	15 A 125-250 VAC 1/2 H.P. 125-250 VAC
Standard	EN 60529 Degree of Protection IP20, 971-SWNO210 & 971-SWNO210A are NEMA type 1, 4X, 6 & 6P - UL Enclosure 1, 4X, 6 & 6P, and IP68
Size	4 x 3 7/16 x 1 5/32 Inch
Weight Approx.	3.6 Oz.
Weight Approx.	Metal Aquiline .9 lbs