


BNC Plug



Dimensions : Millimetres (Inches)

Specifications:

- Bodies : Brass per JIS-C3604
- Centre Contact : Brass per JIS-C3604
- Insulation : Teflon per ASTM D1457 and ASTM D1710
- Part to be clean and free of burrs

BNC Plug



Specification Table

Number	Description	Material	Finish	Part Number
1	Shell	Zinc	Nickel 100 µ Inches Minimum	13-06-4 RG179
2	Insulation	Teflon	None	
3	Gasket	Rubber		
4	Washer	Brass	Nickel 100 µ Inches Minimum	
5	Spring Washer	SK-5		
6	Washer	Brass		
7	Body I			
8	Centre Contact		Gold	
9	Body II		Nickel 100 µ Inches Minimum	
10	Nut I			
11	Chassis			
12	Braid Clamp	Rubber		
13	Gasket		None	
14	Washer		Brass	
15	Nut II	Nickel 100 µ Inches Minimum		

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.