

## Datasheet

Item No. 80.010.0007.0

Relay module WRS-REL-1S-48V20M

relay output modules, contact Assignment: 1 normally open contact,  
input voltage: 24 V AC/DC,output voltage: maximum 48V DC,output  
current: maximum 20 mA DC

Item No.	80.010.0007.0
EAN	4015573322486
order unit	10 Piece(s)

## Technical data

### General

Connection type	Screw connection
Number of normally open contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

### Technical data

Rated frequency, auxiliary-/control circuit	50 - 60
Min. rated frequency, auxiliary/control current circuit	50 Hz
Max. rated frequency, auxiliary/control current circuit	60 Hz
Nominal voltage DC	24 V
Lower nominal voltage DC	20.4 V
Upper nominal voltage DC	26.4 V

### Dimensions

Depth	58.3 mm
Width	12.5 mm
Height	80 mm

## Accessories

Item. No.	Typ:	Description:
-----------	------	--------------

## Drawings