

MaxGrip M3 Plug, Yellow - PS5965Y

Straight Blade Plug 2pole 3wire 15amp 125v



FEATURES

- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.

Specifications

DIMENSION INFO

Pass & Seymour

PS5965Y

Width U S: 1.34"

Height U S: 1.83"

LISTING AGENCY INFO

cULus

UL 39121402

BUY AMERICAN ACT COMPLIANCE

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant