

H2,5/19D BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Order No.	9019170000
Type	H2,5/19D BL
Version	Wire end ferrule, 2.5 mm ² , 12 mm. Colour code: DIN, Blue
GTIN (EAN)	4008190178024
Qty.	500 pc(s).

H2,5/19D BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Length	19 mm	Net weight	0.18 g
--------	-------	------------	--------

Product data

Conductor cross-section	2.5 mm ²	Wire connection cross section AWG, max.	AWG 14
Contact surface length (L2)	12 mm	Contact surface diameter (D1)	2.2 mm
Collar diameter (D2)	4.2 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm		

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
UNSPSC	31-16-31-02	eClass 4.1	27-06-07-01
eClass 5.1	27-40-02-01	eClass 6.0	27-40-02-01
eClass 7.0	27-40-02-01		

Product information

Description of article	Wire end ferrule with plastic collar, blue
------------------------	--

Approvals

Approvals

