

6.02264.75 PowerMaxx ASE

10.8 Volt Cordless Sabre Saw PowerMaxx ASE

- To saw wood, plastics, metal pipes and profiles and much more.
- Light, extremely handy saw for operation with one hand or both hands
- Especially suitable for working in places that are difficult to reach
- Variospeed (V) electronics for variable stroke rate
- Metabo "Quick" no-tool saw blade change function
- Extended range of application thanks to unique quick retainer for sabre saw blades and jigsaw blades
- Depth guide can be adjusted without tools for the ideal utilisation of all the saw blade and diverse applications such as plunge cuts
- Integrated LED work light for optimum illumination of the cutting line
- Practical capacity display for checking the charge status
- Metabo Ultra M technology: Intelligent battery management for long-lasting battery packs with a 3 year guarantee

Comparative technical values

Type of battery pack	Li-ion
Battery pack voltage	10,8 V
Strokes in idle	0 - 3.100 /min
Saw blade stroke	13 mm
Weight (including battery pack)	1,2 kg

Scope of delivery

jigsaw blade for wood and metal, jigsaw blade for metal, 2 Li-Power rechargeable battery packs (10.8 V/4.0 Ah), Charger LC 40, MetaLoc case