

TLS PC Link™ Thermal Labeling System

www.BradyID.com/tls2200

TLS 2200 Printer Specifications

Label Types/ Application Functions	Banner Portrait, Banner Landscape, Wire, Patch Panel, Terminal Block, Desi Strip, Fixed Length
Applications	Circuit Board Labeling, Data Communications Labeling, Safety & Maintenance ID, General & Industrial Labeling, Healthcare ID, Laboratory ID, Panel ID, Security ID, Wire & Cable Marking
Print Technology	Thermal Transfer
Print Resolution	203 dpi
Print Speed	12 mm/sec
Color Capability	Single Color Printing
Max Labels per Day	750 labels/day
Keyboard	None
Backlit Screen	No
Portability	No
Weight	2.50 lbs
Power Supply	Rechargeable Battery, AC Power (optional)
PC Connect Printing	Yes - Serial
Stand Alone Printing	No
Compatible Software	Labelmark™ Software, Windows® based driver for 3rd party software use*
Memory	None
File Transfer from PC to printer	No
Continuous vs. Die Cut Labels	Continuous and Die Cut Labels
Materials Supported	Continuous, Die Cut, Bulk, Over 700 stock parts/custom
Tape Widths	Various sizes from 0.250" to 2.000"
Max Label Width	2.000"
Max Print Width	1.810"
Label Roll Length	50 ft/ 500 ft bulk
Text Sizes	1 to 19 (4 to 72 pt)
Multi-Line Print	Yes
Print Rotation	Yes
Serialization	Yes
Barcode	None built in
Symbols	None built in
Warranty	1 Year Limited Warranty Included

Use the power of your PC for more versatile labeling options.

The Brady TLS PC Link™ thermal labeling system is the best value desktop printing system. The small footprint and lightweight, rugged design makes it a nice fit for a variety of medium volume (approximately 500 labels per print run) applications. It connects to a PC for use with LabelMark™ software (included) or other Windows based programs.

The same basic design as the TLS 2200® allows you to utilize the same consumables (including bulk rolls) in both the TLS 2200 and the TLS PC Link.

Smart-Cell Technology makes printing fast and easy. No calibration is required since the printer automatically formats the label. In addition, the printer has its own printer control language allowing the unit to be integrated with other PC controlled equipment.



Versatile Label Options

Uses all of the available TLS 2200 printer materials and ribbons, including bulk roll material.

LabelMark™ Software Included

Easy-to-use LabelMark™ Labeling Software is included with your TLS-PC Link.

Windows™ Driver Included

This driver allows you to easily print labels from either Brady labeling software solution.



Your Complete Printing Solution:

TLS PC Link Label Rolls Page 24-52
 TLS PC Link Print Ribbons Page 53

Catalog Number	Description
TLSPC	TLS PC Link Thermal Labeling System*
TLSPC-AC	Replacement power supply/battery charger
TLSPC-BP	Rechargeable battery pack
TLSPC-CABLE	Communications cable
PCK-5	Cleaning Kit (includes 5 cleaning cards)

*Includes LabelMark™ labeling software, rechargeable battery pack, power supply/battery charger, R6210 ribbon, sample labels (PTL-19-423), Quick Start Guide, manuals, communications cable, Windows drivers and 1 year Limited Warranty.



Did You Know?

Bulk labels are designed for the TLS 2200 and TLS PC Link thermal labeling systems to save customers money, and provide the perfect low volume* labeling solution.

A reusable dispenser box protects labels from dust and debris and allows easy storage until the next identification job.

Watch for label catalog number that begin with "B". This indicates materials rolls that are "Bulk" label rolls.

* TLS 2200 and TLS PC Link printers are recommended for printing 500 or less labels per print run. Printer slowdown is possible if printing large quantities of labels at one time depending on the material, label size and amount of print coverage.

