

Suggested text for new product proposals - Weatherproof range.



THA.211.A1A3PTK


This cable splitter box is supplied as a complete kit which contains a unique 3 pole terminal block manufactured in a T configuration. This saves time and effort as none of the cables require forming on entry since the connections required are aligned with each of the cable entry points.

Capable of taking cable sizes between 5 and 17mm diameter, the box is manufactured from PA66 UL94 V2 material and is IP65 rated. The 3 pole ENEC approved terminal block will accept conductors up to 4mm Sq and is rated at 32A at 450V.

Features and benefits-

- Large 3 port Teebox, robust construction, easy to use
- Environmentally protected to IP65
- Wide operational temperature range
- Wide cable diameter acceptance range
- Unique 3 face terminal block makes product cabling easy and fast – no special forming of conductor cables.
- Supplied as a ready to use kit.

Terminal Material	Red PA66 UL94V0
No. of poles	3
Max Current	32A
Max Voltage	450V
Operating Temp.	-20 to +125 C
Cable clamping o/d	5-17mm Dia.
Maximum conductor size	4mm Sq.
Box IP rating	IP65
Approvals	IMQ, ENEC



LD

