

4, 5, 6 and 8-Pin Receptacles, Rear Mount with PCB Pins

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 250 V, 4 A (4 & 5 pole)
- 60 VAC/75 VDC (6 pole)



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p><b>FKFD ..</b></p> <p>Typical panel cutout is 15.3 x 14 mm.</p>	FKFD 4.4	FSFD 4.4	105°C, mates with 4-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>
<p><b>FKFD 4.5</b></p> <p>Typical panel cutout is 15.3 x 14 mm.</p>	FKFD 4.5	FSFD 4.5	105°C, mates with 5-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>
<p><b>FSFD ..</b></p> <p>Typical panel cutout is 15.3 x 14 mm.</p>	FKFD 6	FSFD 6	105°C, mates with 6-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>
<p><b>FKFD 8</b></p> <p>Typical panel cutout is 15.3 x 14 mm.</p>	FKFD 8	FSFD 8	105°C, mates with 8-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>

Standard housing material is nickel plated brass "FSFD.."; "FSFDV.." indicates stainless steel.