



3-Wire Cordsets, Threaded Coupling Nut

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 125 V, 4 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>PKG ..M**</p>	<p>PKG 3M-* PKW 3M-*</p>	<p>PSG 3M-* PSW 3M-*</p>	<p>AWM, PVC Yellow, 3x24 AWG, 105°C, 4.4 mm OD, Cable #RF50642-*M†, flexlife*</p>	<p>Female</p> <p>1. BN 3. BU 4. BK</p>
<p>PKG 3M-*/S90 PKW 3M-*/S90</p>	<p>PSG 3M-*/S90 PSW 3M-*/S90</p>	<p>AWM, TPU Black, 3x24 AWG, 90°C, 4.4 mm OD, Cable #RF50587-*M†, Cut/Abrasion Immune</p>		
<p>PKG 3M-*/S90/S101 PKW 3M-*/S90/S101</p>	<p>PSG 3M-*/S90/S101 PSW 3M-*/S90/S101</p>	<p>AWM, TPU Black, 3x24 AWG, 90°C, 4.5 mm OD, Cable #RF51166-*M†, Cut/Abrasion Immune, flexlife-20, High Flex - Over 20 Million Cycles</p>		
<p>PKG 3M-*/S90/S618 PKW 3M-*/S90/S618</p>	<p>PSG 3M-*/S90/S618 PSW 3M-*/S90/S618</p>	<p>AWM, TPU Black, 3x24 AWG, 90°C, 4.4 mm OD, Cable #RF50601-*M†, Cut/Abrasion Immune, EMI/RFI Protection</p>		
<p>PKG 3M-*/S1587 PKW 3M-*/S1587</p>	<p>PSG 3M-*/S1587 PSW 3M-*/S1587</p>	<p>AWM, TPE Yellow, 3x24 AWG, 105°C, 4.4 mm OD, Cable #RF51271-*M†, weldlife*, Weld Flash Immune</p>		
<p>PKG 3M-*/S760 PKW 3M-*/S760</p>	<p>PSG 3M-*/S760 PSW 3M-*/S760</p>	<p>AWM, PVC Black, 3x24 AWG, 4.4 mm OD, Cable #RF50585-M†, flexlife</p>		
<p>PKG 3M-*/S90/S1084 PKW 3M-*/S90/S1084</p>	<p>PSG 3M-*/S90/S1084 PSW 3M-*/S90/S1084</p>	<p>AWM, TPU Black, 2x24 AWG, 90°C, 4.4 mm OD, Cable #RF51197-*M†, Cut/Abrasion Immune, Shielded</p>		
<p>PKG 3M-*/XOR PKW 3M-*/XOR</p>	<p>PSG 3M-*/XOR PSW 3M-*/XOR</p>	<p>PVC, Orange, 3x24 AWG, 80°C, 250°C short term, 4.4 mm OD, Cable #RF04449-*M†, Weld Flash Immune, High Temp. Immune</p>	<p>Male</p> <p>1. BN 3. BU 4. BK</p>	
<p>PKG 3F-..**</p>	<p>PSG 3F-*</p>	<p>AWM, PVC Yellow, 3x24 AWG, 105°C, 4.4 mm OD, Cable #RF50642-*M†, Fixed coupling nut</p>		

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters.
 ** Standard coupling material is nickel plated brass.. "PKG.M"; "PKG.V.M" indicates stainless steel.
 † See Section N for **reelfast**® cable information.

Cordsets