

**Device markers  
LM MT300 26X10 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

**General ordering data**

Order No.	<a href="#">1686401687</a>
Type	LM MT300 26X10 GE
Version	Device markers, Label, 26 x 10 mm, Polyester, PVC-free, Colour: Yellow
GTIN (EAN)	4008190494025
Qty.	10 pc(s).

**Device markers  
LM MT300 26X10 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	26 mm	Width	10 mm
Net weight	12.3 g		

**Markings**

Adhesive	Permanent acrylic copolymer	Can be labelled with thermal transfer printers	No
Can be printed with plotter	Yes	Can be written with dot-matrix printer	No
Can be written with laser printer	Yes	Colour	Yellow
Conductor O.D.	-	Material	Polyester, PVC-free
Material colour according to resistance code	4	Number per sheet	156
Operating temperature range, max.	150 °C	Operating temperature range, min.	-45 °C
Pin can be written (STI)	Yes	PrintJet	No
Printing method	Laser print	Speed marking laser	No
UL 94 flammability rating	HB	Version	Self-adhesive

**Classifications**

ETIM 2.0	EC001288	ETIM 3.0	EC001288
UNSPSC	30-21-18-01	eClass 4.1	24-19-02-18
eClass 5.1	27-14-91-29	eClass 6.0	27-14-91-29
eClass 7.0	27-14-91-29		

**Approvals**

Approvals