

**BRUSHLESS
MOTORS**



**LONGER
MOTOR LIFE**

**MORE
POWER**

**MORE
RUN-TIME**

[LEARN MORE ▶](#)



[Home](#) > [Products](#) > [Tools](#) > [Cordless Tools](#) > [M12™ Cordless LITHIUM-ION System](#) > [M12™ Cordless LED Work Light](#)

M12™ Cordless LED Work Light 49-24-0146

5.0 [Read 3 Reviews](#) [Write a Review](#)



The M12™ Cordless LED Work Light outlasts and outperforms all other subcompact lights. Powered by an M12™ RED LITHIUM™ battery, the work light is 2X brighter and whiter than conventional incandescent bulbs and runs up to twice as long. With a sealed aluminum head to provide impact and weather resistance, Milwaukee® provides a limited lifetime LED warranty. A magnetic back allows hands-free use while a 90 degree rotating head allows the user to easily point the light beam at the desired work area.

Includes

- 49-24-0146-M12 LED Work Light Bare Tool Only
- Warranty-Limited Lifetime LED



FEATURES

- Aluminum Head – Impact and weather resistant
- 90° Rotating Head – Aims light at work space
- Magnetic Back – Hands-free use
- M12 – Works with Milwaukee M12™ RED LITHIUM™ Battery

SPECIFICATIONS

Voltage	12V
Color Temperature	5600K
Lumen	160
Battery	M12™ RED LITHIUM™ (Sold separately)
Length	8.5"
Tool Weight	0.9 lbs

RELATED ARTICLES

Milwaukee® Introduces
New M12 Cordless LED
Work Light

REVIEW SNAPSHOT® by PowerReviews

5.0 (based on 3 reviews) 100% of respondents would recommend this to a friend.

PROS Durable (3) High power output (3)

CONS

BEST USES