


Fixed Shelves

D-4451 Adjustable Fixed Shelf



Adjustable fixed shelf is ideal for installing equipment that cannot be rack mounted.

Adjusts to multiple mounting depths from 19" - 32".


Perforated for additional cooling.

Sturdy 14-gauge steel construction. 75-lb. capacity.

Fits 19" panel width.

Finish: Semi-gloss black

D-6064 Fixed Shelf



| CATALOG NUMBER | A | B | C | D (Depth) | E |
|----------------|-------|-------|-------|-----------|-------|
| D-6064-19x18 | 19.06 | 18.31 | 17.88 | 17.94 | 16.81 |
| D-6064-19x20 | 19.06 | 18.31 | 17.88 | 19.94 | 18.81 |
| D-6064-19x22 | 19.06 | 18.31 | 17.88 | 21.94 | 20.81 |
| D-6064-19x24 | 19.06 | 18.31 | 17.88 | 23.94 | 22.81 |
| D-6064-19x26 | 19.06 | 18.31 | 17.88 | 25.94 | 24.81 |
| D-6064-19x28 | 19.06 | 18.31 | 17.88 | 27.94 | 26.81 |
| D-6064-24x18 | 24.06 | 23.31 | 22.88 | 17.94 | 16.81 |
| D-6064-24x20 | 24.06 | 23.31 | 22.88 | 19.94 | 18.81 |
| D-6064-24x22 | 24.06 | 23.31 | 22.88 | 21.94 | 20.81 |
| D-6064-24x24 | 24.06 | 23.31 | 22.88 | 23.94 | 22.81 |
| D-6064-24x26 | 24.06 | 23.31 | 22.88 | 25.94 | 24.81 |
| D-6064-24x28 | 24.06 | 23.31 | 22.88 | 27.94 | 26.81 |
| D-6064-30x18 | 30.06 | 29.31 | 28.88 | 17.94 | 16.81 |
| D-6064-30x20 | 30.06 | 29.31 | 28.88 | 19.94 | 18.81 |
| D-6064-30x22 | 30.06 | 29.31 | 28.88 | 21.94 | 20.81 |
| D-6064-30x24 | 30.06 | 29.31 | 28.88 | 23.94 | 22.81 |
| D-6064-30x26 | 30.06 | 29.31 | 28.88 | 25.94 | 24.81 |
| D-6064-30x28 | 30.06 | 29.31 | 28.88 | 27.94 | 26.81 |

Finish: Semi-gloss black.

Mounting hardware included.

Material: 14-gauge C.R.S. (.074").

Contact factory for optional perforated ventilation