









[Back](#)

**Selected Cable: 17270A**

| End View   | Plug  | Cord  | Connector   | End View   |
|--|---|---|---|--|
|  |  |  |  |  |
| C14  | 150   | SJT   | 250A  | C13  |

|                                   |  |
|-----------------------------------|--|
| <b>Part Number</b>                | 17270A   |
| <b>Category</b>                   | 3 conductor plastic detachable special use cords             |
| <b>Jacket Color</b>               | black  |
| <b>Length Feet</b>                | 6': 2' legs  |
| <b>Temperature Rating</b>         | 60 C°  |
| <b>Packaging Units Per Carton</b> | B-50   |
| <b>Color Coding</b>               | North America  |
| <b>AWG Stranding</b>              | 16 (65x34)   |
| <b>Nominal OD Inch</b>            | 0.340  |
| <b>Nominal OD millimeter</b>      | 8  |
| <b>Rating</b>                     | 3250 Watts 13A-250V  |
| <b>Notes</b>                      | See 17268A for 18 gauge version. See 17271A for 10' version. |

**Cord View**



**Approvals**



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

