








[Back](#)

Selected Cable: 17508

End View	Plug	Cord	Connector	End View
				
5-15P	290D	SJT	910	C13

Part Number	17508
NSN	6150-01-215-1013
Category	3 conductor plastic detachable
Shielding	unshielded
Jacket Color	black
Length Feet	6'7"
Length Meters	2
Temperature Rating	60 C°C
Packaging Units Per Carton	H-100,H-25
Color Coding	International
AWG Stranding	16 (26x30)
Nominal OD Inch	0.34
Nominal OD millimeter	8.64
Rating	1625 Watts 13A-125V
Notes	See 17509 for 9'10" version. See 17506 for 18 gauge version.

Cord View



Approvals



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

