




[Back](#)

Selected Cable: 17521				
End View	Plug	Cord	Connector	End View
				
NONE	3"STRIP	SJT	386E	C13

Cord View



Part Number	17521
Category	3 conductor plastic original equipment cords
Shielding	unshielded
Jacket Color	black
Length Feet	9'10"
Length Meters	3
Temperature Rating	60 C°C
Packaging Units Per Carton	H-50,H-25
Color Coding	International
AWG Stranding	16 (26x30)
Nominal OD Inch	0.34
Nominal OD millimeter	8.64
Rating	1625 Watts 13A-125V (*)
Notes	See 17520 for 6'7" version. See 17519 for 18 gauge version. See 17621 for shielded version. 17521 is dual rated at 13A-250V.

Approvals



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

