




[Back](#)

Selected Cable: 17461

End View	Plug	Cord	Connector	End View
5-15P	290B	SJ	108	5-15R

Part Number	17461
Category	extension cords rubber and plastic
Jacket Color	black
Length Feet	10'
Length Meters	3.05
Temperature Rating	60 C°C
Packaging Units Per Carton	S-15
Color Coding	North America
AWG Stranding	16 (26x30) [1.52]
Nominal OD Inch	0.34
Nominal OD millimeter	8.64
Rating	1625 Watts 13A-125V
Notes	Restricted use only. Special Use Cord for equipment with built-in receptacle with blades and grounding pin for cord attachment.

Cord View



Approvals



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

