



General Information

Kit Part Number:	2110855-3
Description:	Through Hole Flat Straight and Right Angle Header and Closed End IDC Connector Kit
Application:	Appliance Industries, Coin Changers, Fitness Equipment, Garage Door Openers, Gasoline Pumps, Vending
Family:	MTA-100
TE Brand:	AMP Products
Solution:	Off the Board
Product Type:	Wire-to-Board Connectors
Number of Pieces:	48
RoHS:	Yes

Specifications

Circuit Size(s):	2, 3, 4, 6, 8, 10
Connector Type:	Closed End
Current Rating:	5A
Mounting Style:	Through Hole
Orientation:	Straight, Right Angle
Pitch:	2.54mm (.100")
Tool Included:	No
Voltage Rating:	250V
Wire Gauge (AWG):	22

Product Highlights

The MTA-100 IDC connector system is a wire-to-board and wire-to-wire system with contacts in a single row on .100 [2.54mm] centerline. The design features wire feed-through capability for daisy-chain applications.

Features and Benefits

- Connectors and headers for positions 2-28, shrouded headers 2-14
- Terminates 28-22 AWG discrete wire or notched ribbon cable
- Molded ribs on housing prevent reverse mating
- Color coded housing for wire gauge
- Insulation Displacement Contacts (IDC) eliminates need to strip wires
- Connectors and headers, except shrouded headers, are end-to-end stackable
- Contacts are lubricated for fretting corrosion protection
- 250V, 5A contact rating
- Tin, 15 & 30 gold plating options
- Audible latch for wire-to-wire (posted) housings

Applications

- Garage Door Openers
- Gasoline Pumps
- Household Appliances
- Coin Changers
- Vending Machines
- Fitness Equipment





Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
3-644456-2	2	2 Circuit Narrow Flat Straight Header	Datasheet	Details	Search
3-644456-3	2	3 Circuit Narrow Flat Straight Header	Datasheet	Details	Search
3-644456-4	2	4 Circuit Narrow Flat Straight Header	Datasheet	Details	Search
3-644456-6	2	6 Circuit Narrow Flat Straight Header	Datasheet	Details	Search
3-644456-8	2	8 Circuit Narrow Flat Straight Header	Datasheet	Details	Search
4-644456-0	2	10 Circuit Narrow Flat Straight Header	Datasheet	Details	Search
3-644457-2	2	2 Circuit Narrow Flat Right Angle Header	Datasheet	Details	Search
3-644457-3	2	3 Circuit Narrow Flat Right Angle Header	Datasheet	Details	Search
3-644457-4	2	4 Circuit Narrow Flat Right Angle Header	Datasheet	Details	Search
3-644457-6	2	6 Circuit Narrow Flat Right Angle Header	Datasheet	Details	Search
3-644457-8	2	8 Circuit Narrow Flat Right Angle Header	Datasheet	Details	Search
4-644457-0	2	10 Circuit Narrow Flat Right Angle Header	Datasheet	Details	Search
3-640440-2	4	2 Circuit Closed End Connector	Datasheet	Details	Search
3-640440-3	4	3 Circuit Closed End Connector	Datasheet	Details	Search
3-640440-4	4	4 Circuit Closed End Connector	Datasheet	Details	Search
3-640440-6	4	6 Circuit Closed End Connector	Datasheet	Details	Search
3-640440-8	4	8 Circuit Closed End Connector	Datasheet	Details	Search
4-640440-0	4	10 Circuit Closed End Connector	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
58246-1	No
58644-1	No





