



Sample photo

Order symbol: ABS H 95 G
Product nbr: 8784315

Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002297
EI. number:
 Finland 3423467
 Denmark 8212001970
 Italy 7211050
 Sweden 2536726

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	L	W	H
mm:	170	140	95
inch:	6.7	5.5	3.7

Materials:

Material:	ABS
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Accessories:

H-MP	Mounting plate
CHM-3	DIN-35 Mounting rail
DH-3	DIN-35 Mounting rail
FP 22046	Mounting foot kit (4 pcs)

Rating:

Ingress Protection (EN 60529):	IP 66/67
Impact Resistance (EN 50102):	IK 07
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	Yes
Flammability Rating (UL 746 C 5):	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C:	650
NEMA Class:	NEMA 1, 4, 4X, 6, 6P, 12, 13

Certificates:

