

C-S Series

Tips



Probe Specifications

Plunger	Gold-plated hardened BeCu
Body	Gold-plated brass
Spring	Gold-plated BeCu
Ball	Gold-plated stainless steel
Electrical Resistance	<30 milliohms
Maximum Current	5 amps
Plunger Travel	.045 (1.14)

The recommended hole is .0456 (#56 drill) for epoxy mounting.


Spring Force in oz. (grams)

Spring Type	Initial	Working Travel
Standard	1.0 (28)	4.0 (114)

How to Order [\(top\)](#)

For each probe, specify the probe model and tip style as shown in the example below. If required, specify the optional non-standard spring force.

Example:



[Order Form](#)

Tips [\(top\)](#)

