

Double Row Terminal Blocks

Kulka® 605 GP Series

600 Volts



Specifications:

- Base, General Purpose Phenolic, 150° C
- JJ (GDI-30F) Material Available
- Open Back Design (Insulator Strip Required for Voltage Rating)
- Screws, #1/4-28 Binder Head, Slotted
- Terminals, Plated Brass
- 1-6 Poles
- 1-1/8" Centers
- Wire Range With Wire Binding Screw #2-#12 AWG – 90 Amps
- The Suitability Of These Devices For Greater Currents Shall Be Determined In The End-Use Application
- UL Recognized File No. E47811
- CSA Certified File No. LR19766
- CE

Catalog #	# of poles	Dimensions	
		A	B
605 GP 01	1	2.88	2.25
605 GP 02	2	4.00	3.38
605 GP 03	3	5.13	4.50
605 GP 04	4	6.25	5.63
605 GP 05	5	7.38	6.75
605 GP 06	6	8.50	7.88

MM = Dim X 25.4

Hardware Options: (Hardware options may affect ratings - consult factory)

2502 = Stud 1/4 - 28 Brass (.750 H) Nuts Included See Page 93

