

# FPM-5151G FPM-5171G FPM-5191G

## 15" XGA / 17" SXGA / 19" SXGA Industrial Monitors with Resistive Touchscreens, Direct-VGA, and DVI Ports

**NEW**



### Features

- 15" XGA or 17" / 19" SXGA TFT LCDs
- Direct VGA & DVI-D input interface
- Lockable OSD keys with 2 user-defined contrast/brightness settings
- Flat-sealed front panel
- Robust design with anti-rust chassis and aluminum die-cast front panel
- Front accessible USB connector
- Combo RS-232 & USB interface for touchscreen function (optional)
- Supports industrial 10-30 V<sub>DC</sub> power input with Phoenix jack
- Supports panel, wall, desktop, rack or VESA arm mounting
- Front panel is NEMA4/IP65 compliant

### Introduction

The FPM-5000G series provides 15", 17" and 19" color TFT LCD flat panel monitors specifically designed for industrial applications. With a viewing size from 15" to 19", they present ample display areas as well as vivid and sharp images. It features Direct-VGA & DVI-D signal transmission, which allows VGA control cards to be used in your system. The onscreen display allows users to adjust the images on the screen with two user-defined settings. The front access USB connector provides easy access the controller, and the industrial 10-30 V<sub>DC</sub> wide range power support makes this product an excellent option for Factory and Machine Automation display solutions.

### Specifications

#### General

- **Button Controls** OSD control pad on rear side with lockable function
- **Certification** BSMI, CCC, CE, FCC Class B, UL
- **Dimensions (WxHxD)**
  - 5151G: 449.92 x 315.63 x 50.5 mm (17.71" x 12.43" x 2")
  - 5171G: 481.9 x 355.9 x 55 mm (18.97" x 14.01" x 2.17")
  - 5191G: 481.93 x 384.6 x 59 mm (18.97" x 15.14" x 2.32")
- **Enclosure** Front panel: Aluminum and flat-sealed  
Rear cover: Anti-rust coating
- **Mounting** Panel, wall, desktop, VESA arm, or 19" rackmount
- **Power Input** Phoenix Jack - 10 ~ 30 V<sub>DC</sub> input  
Optional external 57 W power adapter, with AC 100 V ~ 240 V input and DC +12 V @ 4.7A output
- **Power Consumption** 18 W + 20% / 31 W + 20% / 32 W + 20%
- **USB** Front USB access for extension
- **Video Port** VGA & DVI-D
- **Weight (Net)** 6 kg (13.22 lbs) / 8 kg (17.63 lbs) / 10 kg (22.04 lbs)

#### LCD Display

- **Display Type** XGA/ SXGA/ SXGA TFT LCDs
- **Display Size** 15" / 17" / 19"
- **Max. Resolution** 1024 x 768 / 1280 x 1024 / 1280 x 1024
- **Max. Color** 16.2M
- **Viewing Angle (H/V°)** 160/130, 170/160, 178/178
- **Luminance (cd/m<sup>2</sup>)** 250 / 380 / 300
- **Backlight Life (hrs)** 50,000
- **Contrast Ratio** 700:1 / 1000:1 / 1300 : 1

#### Touchscreen (Optional)

- **Sensor** AMT
- **Driver** Penmount 6000
- **Type** 8-wire / 8-wire / 5-wire Resistive
- **Interface** RS-232 & USB
- **Lifespan** 10/ 10/ 36 million with a silicone rubber of R8 finger, writing rate is by 250g at 2 times/s
- **Light Transmission** > 80%
- **OS Support** Windows 2000, XP, Vista, 7, XPe, CE and Linux
- **Power Consumption** +5 V @ 100 mA
- **Touch Resolution** Linearity

#### Environment

- **Operation Temperature** 0 ~ 50°C (32 ~ 122°F)
- **Storage Temperature** -20 ~ 60°C (-4 ~ 140°F)
- **Humidity (Storage)** 10 ~ 90% non-condensing
- **Waterproof** Front panel is NEMA4/IP65 compliant
- **Vibration** 5 ~ 500 Hz, 1 Grms (Operating, Random)


### Ordering Information

- **FPM-5191G-X0AE** 19" SXGA Ind. Monitor
- **FPM-5191G-R3AE** 19" SXGA Ind. Monitor w/Resistive TS (RS-232, USB)
- **FPM-5171G-X0AE** 17" SXGA Ind. Monitor
- **FPM-5171G-R3AE** 17" SXGA Ind. Monitor w/Resistive TS (RS-232, USB)
- **FPM-5151G-X0AE** 15" XGA Ind. Monitor
- **FPM-5151G-R3AE** 15" XGA Ind Monitor w/Resistive TS (RS-232, USB)

# FPM-5151G / FPM-5171G / FPM-5191G

## Dimensions

Unit: mm




**Panel Cut-out Dimensions:** FPM-5151G: 424 x 293 mm (16.69" x 11.54")  
 FPM-5171G: 454 x 338 mm (17.87" x 13.31")  
 FPM-5191G: 454 x 338 mm (17.87" x 13.31")

## Accessories

- **FPM-5151G-SMKE** FPM-5151G/5171G Stand Kit
  - **FPM-5191G-SMKE** FPM-5191G Stand Kit
  - **IPPC-6152A-RMKE** IPPC-6152A/FPM-5151G Rack Mount Kit
  - **IPPC-6172A-RMKE** IPPC-6172A/FPM-5171G Rack Mount Kit
  - **IPPC-6192A-RMKE** IPPC-6192A/FPM-5191G Rack Mount Kit
  - **1702002600** Power Cable US Plug 1.8 M
  - **1702002605** Power Cable EU Plug 1.8 M
  - **1702031801** Power Cable UK Plug 1.8 M
  - **1702031836** Power Cable China/Australia Plug 1.8 M
  - **1757002742** Adapter AC 90-264V 57W SPU63-105
- Note: VESA mounting screw length: M4x6mm

## I/O View



## Front Accessible USB Port



## Back View

