

Heavy Duty Terminal Blocks

0987 RZ Series - Deadfront Type

600 Volts



Specifications:

- Base, Thermoplastic, 105° C
- Connector, Copper Alloy, Nickel Plated (TC Tubular Clamp)
- Printed Circuit Contact, Copper Alloy Electro Tin Plated (PC)
- Wire Range #8-#24 Awg – 50 Amps
- Contact Factory For Multiple Wire Combinations
- .475 Centerline Spacing
- UL Recognized File No. #E47811
- CSA Certified File No. LR19766
- **CE** - Wire Range Reduced #10-#24 Awg

Catalog #	# of poles	Dimensions	
		A	B
0987 RZ TC 02	2	0.95	N/A
0987 RZ TC 03	3	1.43	0.48
0987 RZ TC 04	4	1.90	0.95
0987 RZ TC 05	5	2.38	1.43
0987 RZ TC 06	6	2.85	1.90
0987 RZ TC 07	7	3.33	2.38
0987 RZ TC 08	8	3.80	2.85
0987 RZ TC 09	9	4.28	3.33
0987 RZ TC 10	10	4.75	3.80
0987 RZ TC 11	11	5.23	4.28
0987 RZ TC 12	12	5.70	4.75

- For PC version substitute PC for TC in catalog number
- DIN Adaptor is available for 0987 Series

