

Power Block Covers

Specifications:

140/141/142/143/144/145 Series (Figures 1 & 2)

- Material UL Recognized, QMFZ2, 125°C, .06 Clear Protective Plastic
- Two Thread Cutting Screws Furnished Per Cover
- Covers are Slotted for Easy Installation
- RoHS Compliant

132/133 Series (Figure 3)

- Snap on, Hinged Cover, Black Thermoplastic
- UL Recognized, QMFZ2, 125°C
- RoHS Compliant

Dimensions (in):

Catalog #	A	B	Figure #
CC1402	2.75	2.25	1
CC1403	4.00	2.25	
CC1411	0.77	2.40	2
CC1412	1.42	2.40	
CC1413	2.05	2.40	
CC1414	2.68	2.40	
CC1421	1.06	2.75	1
CC1422	1.87	2.75	
CC1423	2.68	2.75	
CC1431	1.78	3.38	1
CC1432	3.31	3.38	
CC1433	4.84	3.38	
CC1441	2.12	4.00	1
CC1442	4.00	4.00	
CC1443	5.87	4.00	
CC1451	2.87	4.50	1
CC1452	5.56	4.50	
CC1453	8.28	4.50	
CH1321	-	-	3
CH1322	-	-	
CH1323	-	-	
CH1331	-	-	3
CH1332	-	-	
CH1333	-	-	

For electronic drawings or 2D/3D CAD data, send request to drawings@marathonsp.com




FIGURE 1




FIGURE 2




FIGURE 3
(Hinged Cover)