

Digital inclinometer

## DNM 60 L Professional



### *Advantages: DNM 60 L Professional*

#### *Precise digital inclinometer*

- Measures precise inclines in degrees, percent or mm/m
- Direction arrows and acoustic signals at 0° and 90° for easy alignment
- Hold/Copy function to hold and transfer the measuring result
- Automatic rotation of the measured values on the display when working overhead
- Audible signal at 0° and 90°
- Easy calibration function for sustained accuracy
- Robust aluminium housing
- Slanted, easy-to-read display
- 2 vials enable use as a spirit level
- More carrying comfort and safety due to shoulder bag

### *Technical data: DNM 60 L Professional*

Length	60 cm
Measurement range	0° – 360° (4 x 90°)
Electronics measurement accuracy 0°/90°	± 0.05°
Electronics measurement accuracy at 1°– 89°	± 0.2°
Measurement accuracy, vials	0.057° = ± 1 mm/m

Length	60 cm
Power supply	1 x 9 V 6LR61
Operating duration, approx.	200 h
Automatic deactivation facility, approx.	5 mins
Weight approx.	0,7 kg
Width	25 mm
Height	60 mm