

# Heat Gun Kit



## Description:

Variable Temperature heat gun kit featuring 2 airflow settings with heat and selectable cool air stage for maximum user control. This model also has a soft grip handle for comfortable operations.

## Specifications:

|   |   |
|---|---|
| Output                                      | : 1,000W  |
| Voltage                                     | : 120V AC/60 Hz   |
| Air Pressure                                | : 1079 pa/0.157 psi   |
| CFM   | : 8½ up to 14.8 Cubin Feet per Minute                           |
| Variable Temperature                        | : Up to 1050°F  |
| 3 Stage Airflow                             | : Cool Air, 140°F, Low Speed, High Speed                        |
| Safety                                      | : Double insulated for safe operation                           |
| Cord  | : 6½ ft. heavy duty industrial grade rubber                     |
| Circuitry                                   | : State-of-the art interconnect block circuitry                 |
| Switch                                      | : Fully enclosed slide switch                                   |
| Element Construction                        | : Reinforced mica composite with ceramic disk                   |
| Element Life                                | : 500 hours+  |
| Impact Resistant Housing                    | : Made of high grade, self-extinguishing Valox for added safety |
| Dimension                                   | : 4.5" Depth 14" Width 15" Height                               |
| Weight                                      | : 3.25lb  |
| Ergonomic handle with comfortable soft grip |   |

## Kit Includes:

- 1 pcs Variable Heat gun (spc20538)
- 1 pcs Nickel plated steel, 75mm spreader nozzle (SPC20540)
- 1 pcs Nickel plated steel, 3922 reflector nozzle (SPC20541)
- 1 pcs Heavey Duty Carrying Case

## Part Number Table

| Description  | Part Number |
|--------------|-------------|
| Heat Gun Kit | SPC20537    |

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of the Group. © Premier Farnell plc 2012.

