

19" ENCLOSURES

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" SUBRACKS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES

170 Series Enclosures

Sturdy lightweight 19" enclosures designed to accept 'full-width' 84E subracks and standard plug-in units.


- Heights from 2U up to 9U
- Constructed in 1mm thick steel
- Supplied with front tilt-feet, rear fixed feet
- Ventilation slots in base and rear panel
- Recessed side handles for comfort and ease transport
- Supplied flat-pack, open front design
- Front options ordered separately



SPECIFICATION

Materials	Shell 1mm thick steel Handles ABS Legs ABS
Standard colours	Shell epoxy paint graphite grey Handles black similar to RAL 9004 Legs dark grey similar to RAL 7016
Standard unit includes	Top & bases covers Two side panels One rear panel Four feet 19" mounting brackets Handles Mounting hardware
Options	19" Front panels Chassis /tray Vented rear panel 19" attachment set

TYPE NO.	U	WIDTH	HEIGHT	LEGTH
NE32060233	2U	489mm	131.5mm	330mm
NE32060245	2U	489mm	131.5mm	450mm
NE32060333	3U	489mm	176mm	330mm
NE32060345	3U	489mm	176mm	450mm
NE32060633	6U	489mm	306mm	330mm
NE32060645	6U	489mm	306mm	450mm
NE32060945	9U	489mm	443mm	450mm



19" Front Panel

- Aluminium, 3mm thick, silver anodised
- Vented & solid profiles



SILVER ANODISED	GRAPHITE GREY	U	DEPTH	B	OPTION
NE32155001	LA32155101	1U	43.1mm	5.9mm	
NE32155021	LA32155111	1U	43.1mm	5.9mm	Vented
NE32155002	LA32155102	2U	88.1mm	5.9mm	
NE32155022	LA32155112	2U	88.1mm	5.9mm	Vented
NE32155003	LA32155103	3U	132.5mm	37.7mm	
NE32155023	LA32155113	3U	132.5mm	37.7mm	Vented
NE32155004	LA32155104	4U	177.0mm	37.7mm	
NE32155024	LA32155114	4U	177.0mm	37.7mm	Vented
NE32155005	LA32155105	5U	221.5mm	37.7mm	
NE32155025	LA32155115	5U	221.5mm	37.7mm	Vented
NE32155006	LA32155106	6U	265.9mm	37.7mm	
NE32155026	LA32155116	6U	265.9mm	37.7mm	Vented
NE32155009	LA32155109	9U	399.2mm	37.7mm	
NE32155029	LA32155119	9U	399.2mm	37.7mm	Vented

