

Uncontrolled document as of December 13, 2012. Refer to website for up to date specifications.

LIGHTS
2610
HeadsUp Lite LED



HeadsUp Lite™ 2610 LED Flashlight

The 2610 provides hands-free light where you need it, when you need it. A dual mode button activates all 3 LEDs for full brightness, or just 1 to extend battery life. The adjustable cloth strap fits comfortably and securely on your head, while the rubber strap grips tightly to hard hats and helmets. Both are included, as well as 3 AAA alkaline cells. The HeadsUp Lite 2610 is ideal for reading maps and light duties around the campsite.

Body Material: ABS Resin
Minimum Pack 1 ea.
Packaged Weight: 6.3 oz.

HeadsUp Lite™ 2610 LED Flashlight Specifications






HeadsUp Lite™ 2610 LED Flashlight Configurations

Cat. #	Description
2610	HeadsUp Lite™ 2610 LED Flashlight (Corded)

HeadsUp Lite™ 2610 LED Flashlight Accessories

Cat. #	Description
2625	Red LED Flashing/Constant Alert Light

	High	Low
LIGHT SOURCE	LED	
BATTERIES	3 AAAAlkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	4.5	
LENGTH	1.49" (3.8 cm)	
WEIGHT w/ BATTERIES	3.2 oz. (0.09 kg)	
WEIGHT w/o BATTERIES	1.9 oz. (0.05 kg)	

	FL1 STANDARD	High	Low
LIGHT OUTPUT		30 LUMENS	14 LUMENS
RUNTIME (hours/min)		19h	47h
BEAM DISTANCE (meters)		28m	19m
PEAK BEAM INTENSITY (candela)		194cd	91cd
WATER RESISTANT		IPX4	IPX4

HeadsUp Lite™ 2610 LED Flashlight Approvals



Class I, Div. 1; Gp. D T1



Ex ia IIB T4 Gb ITS 10.0019X

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
 e-mail: CSR.Consumer@pelican.com • www.pelican.com