

3-1437366-9 Product Details



Product Highlights:

- 1.27 mm Centerline
- Wire Size - Details = 28 AWG (7/36) Stranded
- Number of Conductors = 10
- Ribbon Cable Outside Conductor Spacing = 11.43 mm
- Width = 12.70 mm

Product Type Features:

- [Ribbon Cable Outside Conductor Spacing \(mm \[in\]\)](#) = 11.43 [0.450]
- Color = Color Coded
- Series = Ansley 201G

Electrical Characteristics:

- Voltage Rating (VAC) = 300
- Impedance (Ω) = 100
- Capacitance (pF/ft) = 14.0

Dimensions:

- Width (mm [in]) = 12.70 [0.500]
- Height (mm [in]) = 1.02 [0.040]

Body Features:

- [Insulation Material](#) = PVC

Housing Features:

- Centerline (mm [in]) = 1.27 [0.050]

Configuration Features:

- Number of Conductors = 10

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Wire Size - Details](#) = 28 AWG (7/36) Stranded
- Temperature Range (°C) = -20 – +105

Packaging Features:

- Packaging Quantity = 30 Meters per Reel

Other:

- Brand = AMP