

CATALOG

- Cross Reference
 - Competitive Products
 - Military Spec P/Ns
 - Tyco Brand P/Ns

- Part Number Search
- Document Search
- Product Type Search
- Product Family Search
- Alphabetical Search
- RoHS/ELV Compliance & Alternates
- CAD Model Search
- Brand Search
- Tool Search
- Multiple Part Comparison
- Lead Free Solutions
- Help/Glossary

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Switches, Shunts, and Knobs

↳ **Pushbutton Switches**

Alcoswitch **MSPS103C0** Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Corporate P/N: 1437568-7)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ➤ General Info ➤ Sales Info 	<ul style="list-style-type: none"> ➤ Pricing ➤ Product Availability 	<ul style="list-style-type: none"> ➤ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product View](#)

Searchable Features:	
Brand:	Alcoswitch
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Wave solder capable to 240°C
Product Type:	Switch
Tactile:	No
Configuration (Pole-Throw):	Single Pole - Single Throw
Contact Rating:	0.5A
Process Sealed:	No
Operating Function:	Normally Open, Momentary
Ganged:	No
Series:	MSPS

Other Properties:	
RoHS/ELV Compliance History:	Always was RoHS compliant
Contact Plating:	Silver
Contact Material:	Copper Alloy
Case Material:	Thermoplastic (LCP)
Bushing Length (mm [in]):	6.22 [0.245]
Actuator Material:	Thermoplastic
Temperature Rating:	Standard

Mount Style:	Panel
Mount Angle:	Vertical
Termination Type:	Wire Lugs
ESD Grounding Terminal:	Without
Low Profile:	No
Packaging Method:	Loose Piece
Actuator Style:	Round
Actuator Length (mm [in]):	5.08 [0.200]
Actuator Profile:	Extended
Actuator Color:	Black
Number of Actuators:	Single
Illuminated:	No
Dust Proof:	No
Support Bracket:	Without
Bushing Style:	Threaded
Bushing Diameter:	1/4-40
Snap Action:	No

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

.