

## Honeywell Sensing and Control

Search



### narrow your search

#### Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (21)

#### Technology

- Electromechanical (9301)
- Flexible Heaters (140)
- Microstructure (1486)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

Wireless Switches Offer Unlimited Benefit  
Basic Switches Are Not Created Equal  
Applying Precision Switches  
Sensors for Medical Devices  
New Ways to Measure Torque  
Choosing Safety Switches  
Specifying Hour Meters

#### Need help?

[Click here to contact us](#)

### 53C15K

( Home : Products » Sensors » Rotary Position Sensors » Conductive Plastic Potentiometers » 53 )



Actual product appearance may vary.

53 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 5 kOhm Resistance Value

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Description

The 53 Series is an economical potentiometer made with a rugged construction. It offers a 2 watt power rating and the benefits of a conductive plastic element. It is available in a special construction that accepts a rotary switch (purchased separately).

#### Features

##### Features

- Robust nickel-plated brass shaft and bushings
- Conductive plastic element
- Linear taper
- 25,000 cycle rotational life

#### Potential Applications

##### Potential Applications

- Manual controls (throttle, joystick)
- Electric vehicles
- Personal mobility
- Off-road vehicles
- Welding and heating
- Telecommunications

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

[Login to iCOM](#)  
[Login to Rep/AD Portal](#)  
[Login to Digital University](#)

### News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

[MICRO SWITCH Anniversary site](#)

## Honeywell Sensing and Control

Search



### narrow your search

#### Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (21)

#### Technology

- Electromechanical (9301)
- Flexible Heaters (140)
- Microstructure (1486)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

### Need help?

[Click here to contact us](#)

### 53C15K

( Home : Products : Sensors » Rotary Position Sensors » Conductive Plastic Potentiometers » 53 )



Actual product appearance may vary.

53 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 5 kOhm Resistance Value

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Product Specifications

Potentiometer Type	Industrial
Element Type	Conductive Plastic
Terminal	Solder lug
Power Rating	2 W
Resistance Value	5 kOhm
Resistance Tolerance	± 10 %
Linearity	± 5 %
Bushing Thread	9,53 mm [0.375 in] x 32 NEF-2A
Bushing Length	9,53 mm [0.375 in]
Bushing Type	Standard
Shaft Diameter	6,35 mm [0.25 in]
Shaft Length	50,80 mm [2.0 in]
Shaft Ending	Plain round
Body	27,8 mm [1.094 in] diameter max. except at terminal standoff
Electrical Taper	Linear
Operating Temperature	-55 °C to 120 °C [-67 °F to 248 °F]
Working Voltage (Max.)	500 V
Rotational Life	25000 cycles
Mechanical Rotation	312°
Availability	Global
Series Name	53
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

[Login to iCOM](#)  
[Login to Rep/AD Portal](#)  
[Login to Digital University](#)

### News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

[MICRO SWITCH Anniversary site](#)

For Reference Only

