

Magnetic Products, Inc.

683 Town Center Drive,

Highland, MI 48357

Tel: 248-887-5600

Email: info@mpimagnet.com • **Website:** www.mpimagnet.com

Item # NH130, Neo-Hold Bi-Pole Magnets

\$51.43

Neo-Hold Bi-Pole Magnets

Neo-Hold Bi-Pole Magnet boasts strong gripping force with two (2) poles on the same face. Constructed from Neodymium Iron Boron Magnets and an aluminum pot. Use where clamping forces are required and space is limited. All Neo-Hold Bi-Pole Magnets are diameter x height / thread size / max pull. Measurements are in inches; holding value is in pounds.

0.866 x 0.787 / M6 / 19.8



SPECIFICATIONS

| | |
|-------------------|----------|
| Diameter | 0.866 in |
| Height | 0.787 in |
| Thread Size | M6 |
| Max. Pull | 19.8 lb |
| Package Type | Each |
| Units Per Package | 1 |
| Weight | 1.5 oz |