

4-Wire Cordsets, Heavy Duty

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 600 V, 10 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>RKM ..**</p>	<p>RKM 46-*M WKM 46-*M</p>	<p>RSM 46-*M WSM 46-*M</p>	<p>STOW PVC Yellow, 4x16 AWG, 105°C, 11 mm OD, Cable #RF50538-*M†, flexlife</p>	<p>Female</p>
<p>WKM ..**</p>	<p>RKM 46-*M/S600 WKM 46-*M/S600</p>	<p>RSM 46-*M/S600 WSM 46-*M/S600</p>	<p>SOOW CPE Yellow, 4x16 AWG, 105°C, 11 mm OD, Cable #RF50595-*M†, Weld Flash Immune, Flame Immune</p>	<p>1. BK 2. WH 3. RD 4. GN</p> <p>Male</p>
<p>RSM ..**</p>	<p>RKM 46-*M/S824 WKM 46-*M/S824</p>	<p>RSM 46-*M/S824 WSM 46-*M/S824</p>	<p>TC PVC Yellow, 4x16 AWG, 90°C, 9.6 mm OD, Cable #RF51220-*M†, Tray Rated</p>	
<p>WSM ..**</p>	<p>RKM 47-*M WKM 47-*M</p>	<p>RSM 47-*M WSM 47-*M</p>	<p>STOW PVC Yellow, 4x16 AWG, 105°C, 11 mm OD, Cable #RF50626-*M†, flexlife</p>	<p>1. BN 2. WH 3. BU 4. GN/YE</p> <p>Female</p> <p>Male</p>

* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RKM .."; "RK .." indicates nylon, "RKV .." indicates stainless steel, and "RKVH .." indicates stainless steel hex.

† See Section N for **reelfast**® cable information.