

PANTUM

The new era for printing



P2000 Printer

Monochrome Laser Printer

Print

- Up to 20ppm
- Manual Duplex
- First print <10s
- Up to 1200*600 dpi

20,000
pages



Monthly Duty Cycle

General

- Memory - 8mb
- Connectivity - USB 2.0 full speed
- Duty Cycle (monthly) - 20,000 pgs
- O/S - Windows 2000 to Windows 7

USB 2.0



Easy Connection

Paper Handling

- Media Size - up to A4
- Input - 150 sht cassette
- Output - 100 sht face down
- Weight Range - 60 to 163gsm

20ppm



20 pages per minute A4

“Built to last, Easy to use”

- Monthly Duty Cycle of 20,000 pages, up to 3 times more than comparable printers in a similar class
- Simple one-button operation to cancel prints / print a test page
- Pain free cartridge replacement with straight-forward installation procedure
- Direct paper path, solid metal paper roller bars and hard rubber paper roller grips, to greatly reduce paper jams
- Constructed around a sturdy metal chassis and frame unlike many other printers in a similar class
- Robust printer that deals with day-to-day wear and tear well
- Longer engine life
- Lower vibration which improves clarity of prints and sharpens small text and symbols on documents
- Environmentally friendly, low cost and low carbon footprint design, highly efficient and low ozone emissions
- Built-to-last design and higher capacity toners reduce the total cost of ownership

Consumables

Toner Cartridges

PA-110L

Starter Toner
(supplied with printer)

700
pages



PA-110

Standard Capacity Toner
(ISO Standard / IEC 19752)

100
pages



PA-110H

High Capacity Toner
(ISO Standard / IEC 19752)

2300
pages

