





| Product Details   |                               |  |                         |
|---|-------------------------------|--|-------------------------|
| Model Name  | LP                            | ECCO Group Europe Part Number  | <b>30102470</b>         |
| Internal ERP Description  | BEACON, LP, XEN, 2W, MV, BLUE |  |                         |
| Product Type  | Xenon Beacon                  | Application  | Automotive / Industrial |
| Product Image – Amber beacon only shown   |                               | Product Dimensions   |                         |
|  |                               |  |                         |

| Electrical Characteristics |                             |                     |  |
|----------------------------|-----------------------------|---------------------|--|
| Input Voltage              | 10-100V DC, 20-72V AC       | Input current       | 300mA @ 12V DC, 120mA @ 24V DC<br>77mA @ 48V DC, 66mA @ 60V DC<br>270mA @ 30V AC, 110mA @ 60V AC |
| Frequency                  | 75 FPM                      | Light Source        | Non-replaceable  |
| Flash Mode                 | Single flash                | Flash Pattern       | N/A  |
| Technology                 | Xenon                       | Power rating        | 2 W  |
|                            |                             | Estimated Tube Life | 3,000 Hours  |
| Other features             | Reverse polarity protection |                     |  |

| Photometric Characteristics |   | Polar Plot   |
|-----------------------------|---|--|
| Colour                      | Blue  |  |
| Max intensity at HV0        | 7 cd from top   |  |
| Min intensity               | 2 cd from side  |  |
| Timing Diagram              |  |  |

| Enclosure            |                         |                      |                                  |
|----------------------|-------------------------|----------------------|----------------------------------|
| IP rating            | IP 67                   | Fixing centres       | 45 mm                            |
| Cable exit           | Central base grommet    | Fastening hardware   | 2 x M5 x 14mm studs with M5 nuts |
| Cable dimensions     | 2 x 0.75mm <sup>2</sup> | Packaging            | Thin wall carton                 |
| Recommended Mounting | Upright or 90°          | Max Fastening Torque | 3 N/m                            |
| Weight (unboxed)     | 130g                    | Weight (boxed)       | 150g                             |

| Approvals and Certifications |                    |      |     |
|------------------------------|--------------------|------|-----|
| EMC                          | UN ECE R10-03 6101 | WEEE | Yes |
| CE                           | Yes                | RoHS | Yes |