





Product Details		Product Dimensions	
Model Name	<b>LT</b>	ECCO Group Europe Part Number	<b>31105272</b>
Internal ERP Description	BEACON, LT, XEN, 5W, 230 VAC, AMBER	Application	Industrial
Product Type	Xenon Beacon		
Product Image – Amber beacon only shown			
			

Electrical Characteristics			
Input Voltage	207 – 253Vac	Input current	40mA @ 230Vac
Frequency	90 FPM	Light Source	Non-replaceable
Flash Mode	Single flash	Flash Pattern	N/A
Technology	Xenon	Power rating	5 W
		Estimated Tube Life	3,000 Hours

Photometric Characteristics		Polar Plot	
Colour	Amber		
Max intensity at HV0	14 cd		
Min intensity	14 cd		
Timing Diagram			
			

Enclosure			
IP rating	IP 67	Fixing centres	45 mm
Cable exit	Central base grommet	Fastening hardware	2 x M5 x 14mm studs with M5 nuts
Cable dimensions	2 x 0.5mm <sup>2</sup>	Packaging	Thin wall carton
Recommended Mounting	Upright	Max Fastening Torque	5 N/m
Weight (unboxed)	130g	Weight (boxed)	150g

Approvals and Certifications			
EMC	UN ECE R10-03 6101	WEEE	Yes (marking only for own brand products)
CE	Yes	RoHS	Yes