


TERMSERIES
RSS113024 24VDC-REL1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



TERMSERIES accessories include:

- Spare relay
- Base
- Partition plates
- Cross-connections
- Power-feed modules

General ordering data

Order No.	4060120000
Type	RSS113024 24VDC-REL1U
Version	TERMSERIES, Relais, No. of contacts: 1, CO contact, AgNi, Rated control voltage: 24 V DC, Continuous current: 6 A, Plug-in connection
GTIN (EAN)	4032248252251
Qty.	20 pc(s).

TERMSERIES
RSS113024 24VDC-REL1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Ratings

Conductor connection system	Plug-in connection	Humidity	5...85 % rel. humidity, no condensation
Weight	5 g	UL 94 flammability rating	V-0

Dimensions and weights

Width	5 mm	Height	28 mm
Depth	15 mm	Weight	5 g
Net weight	6 g		

Temperatures

Operating temperature	-40 °C...+85 °C	Storage temperature	-40 °C...+85 °C
-----------------------	-----------------	---------------------	-----------------

Input

Rated control voltage	24 V DC	Rated current DC	7 mA
Coil resistance	3388 Ω ±10 %	Power rating	170 mW
Pull-in (sparkover) / drop-out voltage DC coil	16.8 V / 1.2 V		

Output

Rated switching voltage	250 V AC	Max. switching voltage, AC	250 V
Max. switching voltage, DC making current	250 V 6 A	Continuous current	6 A
Switch-on delay	< 8 ms	Max. switching power	1500 VA
Min. switching power	100 mA / 5 V, 10 V / 10 mA, 24 V / 1 mA	Switch-off delay	< 4 ms
		Max. switching frequency at rated load	0.1 Hz

Contact specifications

No. of contacts	1	Contact design	CO contact
Contact material	AgNi	Mechanical service life	5 x 10 ⁶ switching cycles

Insulation coordination

Clearance and creepage distances for control side - load side	≥ 5.5 mm	Dielectric strength for control side - load side	4 kV _{eff} / 1 min.
Impulse withstand voltage	6 kV (1.2/50 μs)	Protection degree	IP 67

Other technical data

Version	Relay
---------	-------

Further details of approvals / standards

Standards	IEC 61810-1, UL508
-----------	--------------------

Classifications

ETIM 2.0	EC001437	ETIM 3.0	EC001437
UNSPSC	30-21-19-17	eClass 4.1	40-02-06-14
eClass 5.1	27-37-16-01	eClass 6.0	27-37-16-03
eClass 7.0	27-37-16-03		

Creation date January 24, 2013 1:11:03 PM CET

Data sheet...

TERMSERIES
RSS113024 24VDC-REL1U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals





Approvals



**TERMSERIES
RSS113024 24VDC-REL1U**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings



**TERMSERIES
RSS113024 24VDC-REL1U**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)
Screw connection


TERMSERIES accessories include:

- Spare relay
- Base
- Partition plates
- Cross-connections
- Power-feed modules

General ordering data

Order No.	Type	Version	GTIN (EAN)	Qty.
1123330000	TRS 24-230VUC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Screw connection	4032248905614	10 pc(s).
1123270000	TRS 48VUC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Screw connection	4032248905423	10 pc(s).
1123240000	TRS 24VDC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Screw connection	4032248905485	10 pc(s).
1123250000	TRS 24VUC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Screw connection	4032248905713	10 pc(s).

Tension clamp connection


TERMSERIES accessories include:

- Spare relay
- Base
- Partition plates
- Cross-connections
- Power-feed modules

General ordering data

Order No.	Type	Version	GTIN (EAN)	Qty.
1123390000	TRZ 48VUC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Tension clamp connection	4032248905331	10 pc(s).
1123370000	TRZ 24VDC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Tension clamp connection	4032248905324	10 pc(s).
1123450000	TRZ 24-230VUC 1CO EMPTY	TERMSERIES, Continuous current: 10 A, Tension clamp connection	4032248905508	10 pc(s).

**TERMSERIES
RSS113024 24VDC-REL1U**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

[1123380000](#) TRZ 24VUC 1CO EMPTY

TERMSERIES, Continuous 4032248905195 10 pc(s).
current: 10 A, Tension
clamp connection