



DCG412N

18V XR Li-Ion Grinder - Bare Unit

Selling Proposition

- Latest generation premium Grinder featuring new XR Lithium Ion Technology
- Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster
- Powerful & Highly Efficient PM58 DEWALT fan cooled motor with replaceable brushes, delivers up to 7000 rotations per minute for fast cutting and grinding applications
- Steel cut spiral bevel gears provide highest level of durability and low vibration, increasing user productivity
- Low profile jam pot gear case improves gear durability and ergonomics
- Intelligent trigger & lock-off switch for enhanced work safety & control

Standard Equipment

- 2 position side handle
- Keyless protective guard
- Blade wrench
- Battery and charger sold separately

Warranty Specifications

- 3 Year Limited Warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Voltage	Li-Ion 18 V
Max. Disc Diameter	125 mm
Power Output	405 Watts
No Load Speed	7000 rpm
Spindle Thread	M14
Weight	2.2 kg
Length	400 mm
Height	125 mm