



Ethernet Switch Ha-VIS eCon 3062-AD

8-port Ethernet Switch for vertical installation in control cabinets,
including 2 F.O. ports (SC, MM)

| | | | |
|---------------------------------------|---|--|--|
| Unmanaged | IP 30 | PROFINET comatible <input checked="" type="checkbox"/> | EtherNet/IP compatible <input checked="" type="checkbox"/> |
| Number of ports, Copper / Termination | 6x 10/100Base-T(X) / RJ45 (Twisted Pair) | | |
| Number of ports, F.O. / Termination | 2x 100Base-FX / SC-D female | | |
| Input voltage / Termination | 24 V DC / 3-pole, pluggable screw contact (24 V, 0, FE) | | |
| Permissible range (min./max.) | 9,6 V ... 60 V DC | | |
| Input current | approx. 240 mA (at 24 V DC) | | |
| Housing material | aluminium, powder-coated | | |
| Dimensions (W x H x D) | 23 x 130 x 100 mm (without connectors) | | |
| Weight | approx. 0,6 kg | | |
| Working temperature | -10 °C ... +70 °C | | |
| Approvals | UL 508; UL 60 950-1 | | |
| MTBF | 825.000 h | | |

| Identification | Part number | Drawing | Dimensions in mm |
|--|----------------|---------|------------------|
| Ha-VIS eCon 3062-AD Ethernet Switch with 6 RJ45 ports 2 F.O. ports | 20 76 108 3100 | | |