

Productname : HAND WIPES|PC100 Creationdate : 06.12.11 Version : 1.0
 Ref.Nr.: BDS000974_3_20111206 Replaces: BB10040

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

HAND WIPES 100 pieces
 Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaning - Accessories

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
 Touwslagerstraat 1
 9240 Zele
 Belgium
 Tel.: +32(0)52/45.60.11
 Fax.: +32(0)52/45.00.34
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, B.P. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to 67/548/EEC or 1999/45/EC:

Health: not classified
 Physical: not classified
 Environment: not classified
 Other hazards : not classified



Productname : HAND WIPES|PC100
Ref.Nr.: BDS000974_3_20111206

Creationdate : 06.12.11 Version : 1.0
Replaces: BB10040

2.2. Label elements

Risk-phrase(s) : None
Safety-phrase(s) : S2: Keep out of the reach of children.
 S26: In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

Regulation (EC) No 648/2004 on detergents:

Aqua, C9-11 Pareth 8, Dimethyl Gluturate, Isopropyl Alcohol, Dimethyl Succinate, PEG-75 Lanolin, Dimethyl Adipate, Chlorhexidine Digluconate, DMDM Hydantoin Parfum, Iodopropynyl Butylcarbamate, Limonene, Hexyl Cinnamal

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	<5	F,Xi	11-36-67	B
alcohols, C9-11, ethoxylated	68439-46-3		<5	Xn	22-41	
D-Gluconic acid, compd. with N,N"-bis(4-chlorophenyl)-3,12-diimino-2,4,11,13-tetraazatetradecanediimidamide (2:1)	18472-51-0	242-354-0	<0.5	Xn	22	
PERFUME	-		<0.1		38-43-65-50/53	
Carbamic acid, butyl-, 3-iodo-2-propynyl ester	55406-53-6	259-627-5	<0.01	Xn,N	20/22-41-50	
Explanation notes						
B : substance with national established workplace exposure limit						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	<5	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225, H319, H336	B
Explanation notes							
B : substance with national established workplace exposure limit							

(* Explanation phrases : see chapter 16)



Productname : HAND WIPES|PC100
Ref.Nr.: BDS000974_3_20111206

Creationdate : 06.12.11 Version : 1.0
Replaces: BB10040

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water for several minutes Seek medical attention if irritation persists
Contact with skin :	Wash with water and soap. Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting Seek medical advice

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	No adverse health effects expected
Ingestion :	No adverse health effects expected
Skin contact :	Mildly irritating to skin Symptoms : redness and pain
Eye contact :	Mildly irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures



Productname : HAND WIPES|PC100 **Creationdate :** 06.12.11 Version : 1.0
Ref.Nr.: BDS000974_3_20111206 **Replaces:** BB10040

Shut off all ignition sources
 Ensure adequate ventilation
 Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
 If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well ventilated areas
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated place
 Keep out of reach of children.

7.3. Specific end use(s)

Cleaning - Accessories

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm



Productname : HAND WIPES|PC100
Ref.Nr.: BDS000974_3_20111206

Creationdate : 06.12.11 Version : 1.0
Replaces: BB10040

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product.
	Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves (nitrile)
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state :	Paper tissue impregnated with liquid.
colour :	Colorless.
odour :	Citrus.
pH :	6 - 8
Boiling point/range :	Not available.
Flash point :	> 100 °C
Evaporation rate :	Not applicable.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	1.00 g/cm ³ (@ 20°C).
Solubility in water :	Miscible with water
Auto-ignition :	> 200 °C

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid



Productname : HAND WIPES|PC100
Ref.Nr.: BDS000974_3_20111206

Creationdate : 06.12.11 Version : 1.0
Replaces: BB10040

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation : No adverse health effects expected
Ingestion : No adverse health effects expected
Skin contact : May cause irritation.
Eye contact : May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	>2000 mg/kg
		LC50 inhal.rat	>20 mg/l
		LD50 derm.rabit	>2000 mg/kg
alcohols, C9-11, ethoxylated	68439-46-3	LD50 oral rat	1000-1400 mg/kg
		LD50 derm.rabit	>2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	>100 mg/l
		LC50 fish	>100 mg/l
		EC50 daphnia	>100 mg/l
alcohols, C9-11, ethoxylated	68439-46-3	LC50 fish	10-100 mg/l
		EC50 daphnia	5-25 mg/l



Productname : HAND WIPES|PC100 **Creationdate :** 06.12.11 Version : 1.0
Ref.Nr.: BDS000974_3_20111206 **Replaces:** BB10040

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Miscible with water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.
Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information**14.1. UN number**

UN-number : Not classified as hazardous for transport

14.2. UN proper shipping name

Proper shipping name: Not applicable.

14.3. Transport hazard class(es)

Class: Not applicable.
ADR/RID - Classification code: Not applicable.

14.4. Packing group

Packing group: Not applicable.



Productname : HAND WIPES|PC100 **Creationdate :** 06.12.11 Version : 1.0
Ref.Nr.: BDS000974_3_20111206 **Replaces:** BB10040

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: Not applicable.
IMDG - Ems: Not applicable.
IATA/ICAO - PAX: Not applicable.
IATA/ICAO - CAO: Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
EU-directive 99/45/EC
Regulation (EC) No 1272/2008
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R11: Highly flammable.
R22: Harmful if swallowed.
R36: Irritating to eyes.
R38: Irritating to skin.
R41: Risk of serious damage to eyes.
R43: May cause sensitization by skin contact.
R50: Very toxic to aquatic organisms.
R65: Harmful: may cause lung damage if swallowed.
R67: Vapours may cause drowsiness and dizziness.
R20/22: Harmful by inhalation and if swallowed.
R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.



Productname : HAND WIPES|PC100
Ref.Nr.: BDS000974_3_20111206

Creationdate : 06.12.11 Version : 1.0
Replaces: BB10040

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.
The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.
Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

