

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.



HeadsUp Lite™ 2690 LED Flashlight

Regardless of the season, Pelican's new 2690 HeadsUp Lite™ won't leave you in the dark. With 60 lumens of LED light, 10 hours of battery burn time and weighing in at 4.1 ounces, it's brighter, more efficient, compact and lighter than other headlamps in its class. The no-nonsense rotary bezel switch is easy to operate, even when wearing bulky gloves.

The 2690 is made of impact and chemical resistant ABS and it's water resistant for all-weather use. It comes with an adjustable and comfortable cloth strap, as well as a heavy duty rubber strap that will not slip off your climbing helmet. Pelican's new 2690 HeadsUp Lite™ is engineered for those who take the outdoors seriously.

Use your head. Get the 2690 HeadsUp Lite™ from Pelican.

The Pelican 2690 is now ATEX & IECEx underground mining approved.

2690 HeadsUP Lite manufactured prior to April, 2012 were improperly marked with IECEx EXTr test report number rather than the IECEx Certificate number. Other than the use of the ExTR number rather than the required Certificate number in the equipment markings, the equipment is in full compliance with both the ExTR and Certificate.






Body Material: ABS
Minimum Pack 0 ea.

HeadsUp Lite™ 2690 LED Flashlight Specifications

HeadsUp Lite™ 2690 LED Flashlight Configurations

Cat. #	Description
2690	HeadsUp Lite™ 2690 LED Flashlight (Corded)

High	
LIGHT SOURCE	LED
BATTERIES	3 AAA Alkaline (Included)
CHARGE TIME	
VOLTAGE	4.5
LENGTH	2.81" (7.1 cm)
WEIGHT w/ BATTERIES	4.1 oz. (0.12 kg)
WEIGHT w/o BATTERIES	2.8 oz. (0.08 kg)

FL1 STANDARD	High	
LIGHT OUTPUT 	60 LUMENS	
RUNTIME (hours:min) 	10h 30m	
BEAM DISTANCE (meters) 	81m	
PEAK BEAM INTENSITY (candela) 	1664cd	
WATERPROOF & SUBMERSIBLE 	IPX7	IPX7

HeadsUp Lite™ 2690 LED Flashlight Approvals



I M1 Ex ia I Ma, II 1 G Ex ia IIC T4 Ga, Ex ia IIIC T65°C Da IP65
Certificate: TRL 08ATEX11184X



IECEx TRC 11.00 10X Ex ia I Ma, Ex ia IIC T4 Ga, Ex ia IIIC T65°C



Class I II III, Div. 1 GRPS ABCDEFG T4



Class I II III, Div. 1 GRPS ABCDEFG T4

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
 e-mail: CSR.Consumer@pelican.com • www.pelican.com