

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.



MityLite™ 2340 Flashlight

The 2340 is a compact, convenient personal flashlight, but is also a powerful professional duty light. A pre-focused Xenon lamp module produces a powerful, bright white, modified spot beam. The body is made of unbreakable Xenoy that resists chemicals and water. The MityLite 2340 has a tail button for easy on/off or intermittent light. It is powered by 2 AA alkaline cells and safety approved for hazardous conditions. A must-have for every toolbox.

Body Material: Xenoy Polymer Resin

Minimum Pack 6 ea.






Packaged Weight: 4.2 oz.

MityLite™ 2340 Flashlight Specifications

MityLite™ 2340 Flashlight Configurations

Cat. #	Description
--------	-------------

High		
LIGHT SOURCE	Xenon	
BATTERIES	2 AA Alkaline (Included in select packaging)	
CHARGE TIME	N/A	
VOLTAGE	3	
LENGTH	6.25" (15.9 cm)	
WEIGHT w/ BATTERIES	3.5 oz. (0.1 kg)	
WEIGHT w/o BATTERIES	1.86 oz. (0.05 kg)	

FL1 STANDARD	High	
LIGHT OUTPUT 	10 LUMENS	
RUNTIME (hours/min) 	4h 30m	
BEAM DISTANCE (meters) 	43m	
PEAK BEAM INTENSITY (candela) 	461cd	
WATER RESISTANT 	IPX4	IPX4

2340 MityLite™ 2340 Flashlight (Carded)

NSN List

NSN #	Description
6210-01-417-4076	2340BNVG Black
6210-01-417-4076	2340 Black
6230-01-510-1926	2340

MityLite™ 2340 Flashlight Accessories

Cat. #	Description
722	Helmet Light Holder
750	Helmet Light Holder
760	Helmet Light Holder
770	Universal Helmet Light Holder
2304	MityLite™ 2340 Lamp Module
2357	Cordura® Holster

MityLite™ 2340 Flashlight Approvals



Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.



Class I, Div. 2; Gp. ABCD, T3A.



Ex ib e IIC T4 IP67 IEC Ex TSA 06.0021X



Class I, Div. 1; Gps. C, D T3, Conforms to STD UL783

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: CSR.Consumer@pelican.com • www.pelican.com