

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.



VB3 2220 LED Flashlight

The VB3 2220 LED Flashlight has dual super bright white LEDs that may never need replacing and provide over 30 hours of run time. Light turns on when the head is flipped up. It also pivots to a full 180° for aiming light where you need it. The built-in clip attaches to surfaces up to 1/2" thick. 2 CR2032 3V Lithium coin cells are included.

Body Material: Xylex Polymer Resin

Minimum Pack 6 ea.

Package Weight: 1.7 oz.






VB3 2220 LED Flashlight Specifications

VB3 2220 LED Flashlight Configurations

Cat. #	Description
--------	-------------

High		
LIGHT SOURCE	LED	
BATTERIES	2 CR2032 Lithium (Included)	
CHARGE TIME	N/A	
VOLTAGE	3	
LENGTH	3.5" (8.9 cm)	
WEIGHT w/ BATTERIES	1 oz. (0.03 kg)	
WEIGHT w/o BATTERIES	0.88 oz. (0.02 kg)	

2220	VB3 2220 LED Flashlight (Carded)
2220B	VB3™ 2220 LED Flashlight (Boxed)
2220M	VB3 2220 LED Flashlight Merchandiser Display

FL1 STANDARD		High	
LIGHT OUTPUT		9 LUMENS	
RUNTIME (hours/min)		34h	
BEAM DISTANCE (meters)		12m	
PEAK BEAM INTENSITY (candela)		38cd	
WATER RESISTANT		IPX4	IPX4

VB3 2220 LED Flashlight Approvals



Listed 4S67/E184884 Class I, Div. 1 Gps.A,B,C,D, T6.



Ex ib IIC T6 Gb IECEx ITS 10.0021

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
 e-mail: CSR.Consumer@pelican.com • www.pelican.com