



GEN2800 Generator

Generator Specification:

Type:

Self-Exciting, 2-Pole,

Field Rotating Type

AC/DC:

AC Output

Switchable Voltage:

110v (21A) / 230v (10.5A)

Power Rating (Continuous) 50Hz:

2.4kw / 3kVA

Power Rating (Max.) 50Hz:

2.8kw / 3.5kVA

Weight:

20.1kg

Total Harmonic Distortion:

25% THD

Features:

Thermal Cut-Outs

Automatic Voltage Regulation (AVR)

Product Dimensions (H x D x W):

305 x 340 x 260mm

Packaging Dimensions (H x D x W):

340 x 318 x 350mm

Engine Unit Specification:

Engine Brand:

Evolution

Engine Type:

4-Stroke (Single Cylinder)

Engine Displacement:

200cc

Engine Power:

6.5hp

Max Speed:

3150rpm

Fuel Tank Capacity:

3.1L

Starter:

Recoil

Oil Warning:

Oil Low Sensor

Weight:

29.1kg

Wheels (Supplied Detached):

8" Rubber Tyres

Brake:

Manual Foot Brake

Frame:

1" Steel Tubular Frame

Sound Power Level:

98db(A)

Handle:

Fold-away