

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [85791-0020](#)
Status: **Active**
Description: PDJack™ Gigabit POE+ Class 0

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Modular Jacks/Plugs
Series	85791
Component Type	PCB Jack
Magnetic	Yes
Performance Category	5, 5e
Power over Ethernet (PoE)	PoE+
Product Name	Magnetic Jack, PDJack™
UPC	887191157320

Physical

Boot Color	N/A
Color - Resin	Black
Durability (mating cycles max)	750
Inverted / Top Latch	Yes
Jack Height	13.87mm
Lightpipes/LEDs	None
Material - Metal	Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PBT
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	2.03mm
Plating min - Mating	0.762µm
Ports	1
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0°C to +70°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	100V AC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-85791-002
---------------	--------------



EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[85791Series](#)

Mates With

Plugs according to IEC 60603-7

This document was generated on 02/01/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION